



POLINAR 260

INFORMATIVE
DATA SHEET



MEDIUM WEIGHT PACKAGING



AUTOMATIC SEALING MACHINE



SUITABLE FOR LOW TEMPERATURES PACKAGING

POLINAR

COMPOSITION

BACKING: biaxially oriented polypropylene film
ADHESIVE: natural rubber / hydrocarbonic resins / solvent
CORE: recycled paper and paperboard

SUITABLE FOR

Hand dispensers and automatic sealing machines;
sealing of recycled cardboard boxes

AVAILABLE COLOURS

Brown - white - transparent

The quick adhesion at high and low temperatures on all cardboard, the resistance and brilliance typical of polypropylene films, make it ideal for all applications in the packaging sector. It is printable on flexographic machines with primer and release system.



BACKING THICKNESS
32 μm



BREAKING LOAD
> 45 N/cm















ELONGATION AT BREAK
> 116%



POLINAR TAPES

INFORMATIVE
DATA SHEET



	 backing thickness µm	 total thickness µm	 adhesion N/cm	 breaking load N/cm	 elongation at break %	 available colours	 direct print	 heavy weight packaging	 medium weight packaging	 light weight packaging	 automatic sealing machine	 suitable for low temperatures packaging
POLINAR 230	25	43	> 2,0	> 36	> 116	brown / white / transparent				•	•	•
POLINAR 240	28	46	> 2,0	> 39	> 116	brown / white / transparent				•	•	•
POLINAR 260	32	50	> 2,0	> 45	> 116	brown / white / transparent			•		•	•
POLINAR BTS 240	28	46	> 2,0	> 39	> 116	brown / white / transparent	•			•	•	•
POLINAR BTS 260	32	50	> 2,0	> 45	> 116	brown / white / transparent	•		•		•	•
POLINAR 265	32	51	> 2,0	> 45	> 116	red / orange / black / yellow / dark blue / green / light blue			•		•	•
POLINAR 280	40	58	> 2,0	> 54	> 116	brown / transparent		•			•	•
POLINAR HM 230	25	42	> 4,5	> 36	> 116	brown / transparent				•	•	
POLINAR HM 240	28	45	> 4,5	> 39	> 116	brown / white / transparent				•	•	
POLINAR HM 270	35	61	> 6,0	> 47	> 116	transparent			•		•	

It is good practice to use the product within 12 months from purchase date (6 months if jumbo roll). The rolls must be kept in their original packing. Keep the product out of the light and protect from direct heat sources. The tape must be kept in a dry place, at humidity level below 65%, preferably at a temperature between 15° C and 25° C. If the storage temperature is different, restore the tape back to above level before using it.

The values in the informative data sheets are the average results of tests made on our standard production and are not legally binding. The aesthetic and technical features may be subject to some changes caused by ageing, even though the quality level of the product is maintained. Nar shall not be liable for direct damages or for any consequence arising from the misuse of the product. We suggest the verification of the product suitability to the specific condition of use.

Additional indications are available in the last edition of the booklet "Recommendation regarding choice, storing and use of pressure sensitive tapes" published by Federazione Gomma Plastica.



[www.nar-spa.com/
technical-notes.html](http://www.nar-spa.com/technical-notes.html)